

A.

ALTERNATIVE
ARTEFACTS

a.

DANTO

Cell

Designer:Claesson Koivisto Rune Architects
Product Number: CEL




(Top Left) CEL-002 / 150HEX (Top Right) CEL-004 / 150HEX
(Bottom Left) CEL-003 /150HEX (Bottom Right) CEL-001 / 150HEX

Specification

Product name Product code: Cell CEL	Installation method
Category: Standard (*Order)	Bonding method: Adhesive bonding
	Adhesive: *DQZ
Material: B I / Porcelain / Unglazed	Adhesive application method:
Surface colour: Varied	With grouting: 5mm notched
Surface profile: Flat	Without grouting: Flatten 5mm notched
Connection method: Single piece	Standard joint width: 3mm
Place of manufacture: Awaji island	Grouting method: Grouting
Backside: Adhesive bonding only	*DQZ : Modified silicone one-component reaction-curing elastic adhesive
	Installation area
	Interior wall ◎ Interior floor ◎ Bathroom wall ◎
	Bathroom floor × Exterior wall ◎ Exterior floor △
	Frost resistance ◎

Format

Dimensions	Actual dimensions	Thickness	Quantity/sqm	Pieces/box	sqm/box	Weight (kg)/box
150HEX	147×138	9	58.0	50	0.86	18.0




The surface may become slippery depending on the installation environment. Please check the installation environment carefully before use, especially in sloped areas or locations where water exposure is expected.

仕様

製品名 製品記号：Cell CEL	施工方法
生産区分：標準品（* 注文品）	張付け方法：接着剤張り
	接着剤：DQZ
材質：B I / 磁器質 / 無ゆう	接着剤塗布方法：目詰詰めあり：5mm くし目
表面色調：色幅あり	目地詰めなし：5mm くし目平押さえ
表面面状：フラット	標準目地幅：3mm
タイル連結方法：単品	目地施工：塗目地
生産地：淡路島工場	
裏足：接着剤張り専用	使用部位区分
	屋内壁 ◎ 屋内床 ◎ 浴室壁 ◎
	浴室床 × 屋外壁 ◎ 屋外床 △ 耐凍害 ◎

規格

形状記号	形状名	実寸法(mm)	厚さ(mm)	㎡必要枚数(枚)	入数/ケース(枚)	㎡数/ケース	重量(kg)/ケース
150HEX	150ヘキサゴン	147×138	9	58.0	50	0.86	18.0



使用環境により滑りやすくなる場合がございます。
傾斜部や水濡れが想定される場所でご使用の際は、
事前に使用環境をご確認のうえご採用ください。

Cell

Designer:Claesson Koivisto Rune Architects
Product Number: CEL

Colours




CEL-001*



CEL-002



CEL-003




CEL-004

Contact Info

DANTO TILE CO., LTD.
Ama factory: 1290 Igano Kita Ama Minami Awaji Hyogo
Fukura factory: 86 Fukura-Hei Minami Awaji Hyogo
www.aa-danto.com

Items marked with * are made to order (take 2 months or more).

*印は受注生産 (2ヶ月～) になります。



CEL-004 / 150HEX



CEL-002 / 150HEX